


Specification of Pascal mag ejector rod



- It is possible to fix the ejector plate without fault to use the glue for thread locking. (Loctite242 included)
- Need a special tool in order to fit the fixed rod in machine. Contact us in details.

It should be min. 40mm.



- Injection machine might need 2-4 kinds of Pascal mag ejector rods.
- In case that machine uses magnetic clamp or insulation, it might be different from Pascal standard rod length.

Injection machine	Builder :	Model :	Number of production	
Overall length a		Length of Removable rod b	Thread c x d	
ø 26	Short rod 		<input type="checkbox"/> M 1 6 x <input style="width: 40px;" type="text"/>	Fixed rod (short) pieces
	Long rod 		<input type="checkbox"/> M 2 0 x <input style="width: 40px;" type="text"/>	Fixed rod (long) pieces
ø 40	Short rod 		M 3 0 x <input style="width: 40px;" type="text"/>	Removable rod pieces
	Long rod 			Fixed rod (short) pieces
				Fixed rod (long) pieces
				Removable rod pieces

Remarks

Pascal

Customer Service

T E L : +81-72-777-3333 (Overseas sales Dept.)

F A X : +81-72-777-3520

E - m a i l : molding@pascaleng.co.jp